



SERIE SS-ZDG

*High Speed Gauze Swab Folding Machine
(un-folded edge)*



Un-folded edge
gauze swab



Series high speed gauze swab folding machine can meet most of the standard gauze swab folding methods, such like folded edge or un-folded edge, 5x5cm, 7.5x7.5, 10x10cm, 8ply, 12ply, 16ply.

Copyright by LOYAL. This brochure contains photos and technical data for information only, without contractual engagement. LOYAL reserves the right to introduce any modifications in the design and/or equipment.



WUHAN LOYAL MACHINERY CO., LTD

© 5B05, Decheng Center (DECH CENTER), Zhongbei Road No. 124,
Wuchang District, 430061, Wuhan City, Hubei Province, China
Mobile: 0086 1387 1887 978 (WhatsApp / Wechat) Tel / Fax: 0086 27 8566 3380
E-mail: loyal@med-machinery.cn michelle_6237@hotmail.com
www.med-machinery.cn



SERIE SS-ZDG


*High Speed Gauze Swab Folding Machine
(un-folded edge)*

TECHNICAL SPECIFICATIONS



Humidification system makes the gauze swab folding in very good shape.

Electronic sensors monitor the output, give alarm to user if there is any folding mistake been happen, ensure accurate counting.



The gauze material roll tension controlled by magnetic powder clutch, machine running with stable tension.

Copyright by LOYAL. This brochure contains photos and technical data for information only, without contractual engagement. LOYAL reserves the right to introduce any modifications in the design and/or equipment.



WUHAN LOYAL MACHINERY CO., LTD

① 5B05, Decheng Center (DECH CENTER), Zhongbei Road No. 124,
Wuchang District, 430061, Wuhan City, Hubei Province, China
Mobile: 0086 1387 1887 978 (WhatsApp / Wechat) Tel / Fax: 0086 27 8566 3380
E-mail: loyal@med-machinery.cn michelle_6237@hotmail.com
www.med-machinery.cn



SERIE SS-ZDG

*High Speed Gauze Swab Folding Machine
(un-folded edge)*



Via simple adjustment, different tier (4ply, 8ply, 12ply and 16ply) can be done in ONE machine.

Technical Parameter

Folding speed	290-400 pieces/min
Output tracks	2 lanes
Main power	6-10KW
Heating power	2.8KW
Compressor air	0.6MPa

Copyright by LOYAL. This brochure contains photos and technical data for information only, without contractual engagement. LOYAL reserves the right to introduce any modifications in the design and/or equipment.



WUHAN LOYAL MACHINERY CO., LTD

☎ 5B05, Decheng Center (DECH CENTER), Zhongbei Road No. 124,
 Wuchang District, 430061, Wuhan City, Hubei Province, China
 Mobile: 0086 1387 1887 978 (WhatsApp / Wechat) Tel / Fax: 0086 27 8566 3380 3/4
 E-mail: loyal@med-machinery.cn michelle_6237@hotmail.com
 www.med-machinery.cn